



PREMIUM – Optic Low-Speed System with Light and Water Spray

Standard Low-Speed Operative System

Clinical Application	Head	Contra Angle Attachment	Motor Universal "E" Type
Dentin reduction, gross caries removal, general cavity preparation, porcelain adjustments, C & B preps (bevels & margins), cut retention grooves	 <p>68LH Push Button 1:1 Transmission For latch burs Speed up to 20,000 rpm Order #0540.2040</p>  <p>80LD Push Button 1:1 Transmission For FG burs Speed up to 20,000 rpm Order #0540.1830</p>	 <p>20LP 1:1 Transmission Speed range up to 20,000 rpm New hygienic coating Air/water coolant Cellular optic glass rod Order #1001.7453</p> 	

Standard Low-Speed Endo



Clinical Application	Head	Contra Angle Attachment	Motor Universal "E" Type
Root canal treatment with latch type files (ideal from 150 rpm to 270 rpm with Nickel Titanium files), pin drilling & placement, deep caries removal, composite polishing	 <p>62LDN Push Button 10:1 Reduction For latch burs or rotary endo files Speed up to 270 rpm Order #0540.8310</p>	 <p>29LP 7.4:1 Reduction Speed range up to 5,400 rpm New hygienic coating Air/water coolant Cellular optic glass rod Order #1001.7454</p> 	 <p>181L INTRA Air LUX Motor with Light Speed range from 5,000 up to 20,000 rpm. Internal air/water coolant. 6-hole connection. Anti retraction valve. Fits all cellular optic attachments with universal "E" type connection. Order #0535.5210</p> 

-  AIR MOTOR
-  CELLULAR OPTICS
-  WATER COOLANT


Standard Low-Speed Chairside Handpiece

Clinical Application	Straight Handpiece
Chairside trimming, denture adjustment	 <p>10LP 1:1 Transmission Speed range up to 20,000 rpm New hygienic coating Air/water coolant Cellular optic glass rod Order #1001.5660</p> 

Head Options

Clinical Application	Head
Dentin reduction, gross caries removal, general cavity preparation, porcelain adjustments, C & B preps (bevels & margins), cut retention grooves, increased torque	 <p>67LH Push Button 2:1 Reduction For latch burs Increased torque Speed up to 10,000 rpm with attachment 20LP Order #0540.8460</p>
Prophylaxis, (with cups or brushes), composite polishing	 <p>31LR Propy Head 2:1 Reduction For screw in or snap-on cups Speed up to 3,750 rpm with attachment 7LP Order #0549.3380</p>

Attachment Options

Contra Angle Attachment
 <p>7LP 2.7:1 Reduction Speed range up to 7,407 rpm Air/water coolant New hygienic coating Cellular optic glass rod Order #1001.7452</p> 